

GigE Camera Cable RJ45 plug 45° rotated and 90° angled with screws to RJ45 plug Cat.6 S/FTP 3 m black

Description

This network cable by Delock can be used to connect different networking devices, e.g. a NIC to a switch or a patch panel.

RJ45 plug with screws for vision application

The RJ45 plug is equipped with two M2 screws and is compatible with the GigE camera connection. This means the cable can be used for industrial image processing, while the screw-type connectors ensure a firm and secure connection even in the event of movement and vibration.

With angled connector

The angled plugs enable a space-saving installation in tight spaces behind appliances or in machines.



Item no. 80919

EAN: 4043619809196

Country of origin: China

Package: Zip poly bag

Technical details

- Connectors:
 - 1 x RJ45 plug with screws 45° rotated and 90° angled
 - 1 x RJ45 plug
- Cat.6 specification
- 1:1 connected
- Suitable for Gigabit Ethernet vision systems
- Shielded (S/FTP)
- Screw type: M2
- Screw distance: ca. 20 mm
- Cable gauge: 26 AWG
- Cable diameter: ca. 7.0 mm
- Colour: black
- Length incl. connectors: ca. 3 m

Package content

- GigE camera cable

Images



General

Specification:	Cat. 6
Style:	both sides identical

Interface

Connector 1:	1 x RJ45 plug with screws 45° rotated and 90° angled
Connector 2:	1 x RJ45 male

Physical characteristics

Cable gauge:	26 AWG
Shielding:	S/FTP
Length:	3 m
Colour:	black
Cable diameter:	7 mm

Manufacturer information

Street	Beeskowdamm 13/15
Postal code	14167
City	Berlin
Country	Deutschland
E-Mail	info@delock.de
Website	www.delock.de