

RJ45 Flat Patch Cable plug to plug Cat.8.1 flexible 0.25 m black

Description

This network cable by Delock can be used to connect various devices and is suitable for 40GBASE-T Ethernet applications with a frequency of 2 GHz and a data transfer rate of up to 40 Gbps.

Super flexible and flat

The RJ45 cable is ideal for laying under carpets, floors or behind wallpaper. The material of the cable sheath is flexible and makes the cable very resistant to strain.



Item no. 80177

EAN: 4043619801770

Country of origin: China

Package: Zip poly bag

Technical details

- Connectors:
1 x RJ45 plug
1 x RJ45 plug
- Cat.8.1 specification
- Data transfer rate up to 40 Gbps
- Flexible
- Shielded (U/FTP)
- Cable gauge: 32 AWG
- Length incl. connectors: ca. 25 cm
- Colour: black
- Material: TPE

System requirements

- A free RJ45 jack

Package content

- RJ45 cable

Images



General

Specification:	Cat. 8.1
Style:	both sides identical

Interface

Connector 1:	1 x RJ45 male
Connector 2:	1 x RJ45 male

Technical characteristics

Data transfer rate:	Gigabit Ethernet up to 40 Gbps
---------------------	--------------------------------

Physical characteristics

Cable gauge:	32 AWG
Material:	TPE
Shielding:	U/FTP
Length:	25 cm
Colour:	black

Manufacturer information

Street	Beeskowdamm 13/15
Postal code	14167
City	Berlin
Country	Deutschland
E-Mail	info@delock.de
Website	www.delock.de