

19" Industry Hub 13 x USB 5 Gbps Type-A

Description

This solid industry capable USB hub by Delock with metal housing can be connected to a computer via the USB Type-A interface. It expands the computer by 13 USB Type-A ports. The hub can be used for automation and office applications.

USB 5 Gbps specification

With the support of USB 5 Gbps specification a data transfer rate up to 5 Gbps can be reached. Compared to USB 2.0, data can be transferred 10 times faster. All ports are backward compatible, so USB 2.0 and USB 1.1 devices can be used as well.

19" rack mounting

With the supplied mounting brackets, the hub can be mounted in a 19" rack.



Item no. 64039

EAN: 4043619640393

Country of origin: China

Package: Box

Technical details

- Connectors:
 - 1 x USB 5 Gbps Type-B female
 - 13 x USB 5 Gbps Type-A female
 - 1 x 5 V DC jack 5.5 x 2.1 mm
- Chipset: VIA VL813
- Data transfer rate up to 5 Gbps
- Output power: max. 16 W total
- Robust metal housing
- Removable 19" rack brackets
- LED indicator for power
- Operating temperature: 0 °C ~ 60 °C
- Dimensions (LxWxH): ca. 440 x 135 x 45 mm
- Colour: black
- Plug & Play

Power supply specification

- Wall power supply
- Input: AC 100 ~ 240 V / 50 ~ 60 Hz / 1 A

- Output: 5 V / 4 A
- Ground outside, plus inside
- Dimensions:
 - inside: ø ca. 2.1 mm
 - outside: ø ca. 5.5 mm
 - length: ca. 9 mm

System requirements

- Chrome OS 68.0 or above
- Linux Kernel 3.3 or above
- Mac OS 10.14.1 or above
- Windows 7/7-64/8.1/8.1-64/10/10-64
- PC or laptop with a free USB Type-A port

Package content

- Hub USB
- 1 x cable USB 5 Gbps A male to USB 5 Gbps B male, length ca. 1.20 m
- 2 x mounting brackets for 19" rack
- Power supply
- Screws
- Nuts
- User manual

Images



General

Unit height:	2
Function:	Hot Swap Plug & Play
Mounting type:	19 in
Supported operating system:	Chrome OS Linux Kernel 3.3 or above Mac OS 10.14.1 or above Windows 10 32-Bit Windows 10 64-Bit Windows 7 32-Bit Windows 7 64-Bit Windows 8.1 32-Bit Windows 8.1 64-Bit
LED indicator:	Power

Interface

Connector 1:	1 x USB 5 Gbps Type-B female
Connector 2:	13 x USB 5 Gbps Type-A female
Connector 3:	1 x DC jack

Technical characteristics

Data transfer rate:	5 Gbps
---------------------	--------

Physical characteristics

Length:	440 mm
Width:	135 mm
Height:	45 mm
Colour:	black

Power supply

Power supply type:	Euro wall power supply
Power supply output:	5.0 V / 4.0 A
Power supply connector:	DC male 5.5 mm x 2.1 mm

Manufacturer information

Street	Beeskowdamm 13/15
Postal code	14167
City	Berlin
Country	Deutschland
E-Mail	info@delock.de
Website	www.delock.de

