

# Adapter USB Type-C™ male > DVI female (DP Alt Mode) 4K 30 Hz

## Description

This adapter by Delock is suitable for the connection of a DVI monitor to a computer with USB-C™ interface and DisplayPort alternate mode support. Thus, the adapter can be connected to different laptops like MacBook, Chromebook and similar. In addition, the adapter can also be operated on a Thunderbolt™ 3 interface.



20 cm

**Item no. 61213**

EAN: 4043619612130

Country of origin: China

Package: Retail Box

## Technical details

- Connectors:
  - 1 x USB Type-C™ male >
  - 1 x DVI 24+5 female with nuts
- Chipset: Realtek RTD2171U
- DVI-D (Single Link), VGA not wired
- DisplayPort 1.4 specification
- Resolution:
  - DVI up to 1920 x 1080 @ 60 Hz  
(depending on the system and the connected hardware)
  - HDMI with the help of an adapter cable up to 3840 x 2160 @ 30 Hz  
(depending on the system and the connected hardware)
- Transfer of digital video signals
- Supports 3D displays
- Supports HDCP 1.4 and 2.2
- USB bus powered
- Plug & Play
- Connectors: gold-plated
- 1 x ferrite core
- Cable length without connectors: ca. 20 cm
- Colour: black

## System requirements

- Chrome OS
- iPad Pro (2018)
- Linux Kernel 4.3 or above
- Mac OS 10.12 or above
- Windows 7/7-64/8.1/8.1-64/10/10-64/11
- Windows 10 Mobile
- PC or laptop with a free USB Type-C™ port and DisplayPort alternate mode or
- PC or laptop with a free Thunderbolt™ 3 port

---

## Package content

- USB-C™ to DVI adapter

---

## Images



## General

|                             |   |
|-----------------------------|---|
| Function:                   | Plug & Play   |
| Specification:              | DisplayPort 1.4   |
| Supported operating system: | Chrome OS<br>Linux Kernel 4.3 or above<br>Mac OS 10.12 or above<br>Windows 10 32-Bit<br>Windows 10 64-Bit<br>Windows 10 Mobile<br>Windows 7 32-Bit<br>Windows 7 64-Bit<br>Windows 8.1 32-Bit<br>Windows 8.1 64-Bit<br>iPad Pro (2018) |

## Interface

|         |                      |
|---------|----------------------|
| Output: | 1 x DVI 24+5 female  |
| Input:  | 1 x USB Type-C™ male |

## Technical characteristics

|                            |   |
|----------------------------|---|
| Chipset:                   | Realtek RTD2171U  |
| Maximum screen resolution: | 2560 x 1600 @ 60 Hz<br>3840 x 2160 @ 30 Hz<br>4096 x 2160 @ 24 Hz |
| Signal transmission:       | video   |

## Physical characteristics

|                      |             |
|----------------------|-------------|
| Ferrite core:        | 1 x         |
| Cable length:        | 20 cm       |
| Connector finishing: | gold-plated |
| Colour:              | black       |

## Manufacturer information

|             |                   |
|-------------|-------------------|
| Street      | Beeskowdamm 13/15 |
| Postal code | 14167             |
| City        | Berlin            |
| Country     | Deutschland       |
| E-Mail      | info@delock.de    |
| Website     | www.delock.de     |