

goodram

RIVAL

GAMING MICRO CARD

GGSM3AA

MAIN FEATURES

UHS-I U3 interface
 Available capacities: 64, 128, 256 GB
 Up to 100 MB/s read speed¹
 V30 Video Speed Class
 Perfect for 4K video processing
 Extreme durability
 Lifetime warranty



The Goodram RIVAL UHS-I U3 microCARD is the perfect addition to any handheld console. Fast storage expansion allows you to take all your favorite titles with you, without ever worrying about available disk space.

+ PARAMETERS

Available capacities	64, 128, 256 GB
Card standard	Micro SDXC
Max. transfer	read: up to 100 MB/s, write: up to 70 MB/s ²
Card dimensions	15.0 x 11.0 x 1.0 [mm]
Interface speed	UHS-I U3
Video Class Standard	V30
Blister dimensions	103 x 123 [mm]
Operating temperature	-25°C to +85°C
Storage temperature	-40°C to +85°C

+ DETAILS

PRODUCT	CAPACITY	P/N	EAN
GOODRAM RIVAL M3AA	64 GB	GGSM3AA-0640R12	5908267914717
	128 GB	GGSM3AA-1280R12	5908267914731
	256 GB	GGSM3AA-2560R12	5908267914762

¹ Based on internal tests using PCI-e adapter. Speed may vary depending on the testing methodology and platform and operating system.

² Max. write speed for 64GB cards: up to 40MB/s.

goodram

RIVAL

GAMING MICRO CARD

GGSM3AA



LOGISTICS DATA

P/N	EAN	MOQ	PRODUCT DIMENSIONS (mm)	PRODUCT WEIGHT (g)	BLISTER DIMENSIONS (mm)	PRODUCT WEIGHT IN BLISTER (g)	MOQ CARTON DIMENSIONS (mm)	MOQ CARTON WEIGHT (g)	COLLECTIVE PACKAGING DIMENSIONS (mm)	COLLECTIVE PACKAGING WEIGHT (kg)
GGSM3AA-0640R12	5908267914717	25	15.0 x 11.0 x 1.0	0.4	103 x 123 x 7	9.5	124 x 136 x 108	280	515 x 280 x 125	2.5
GGSM3AA-1280R12	5908267914731	25	15.0 x 11.0 x 1.0	0.4	103 x 123 x 7	9.5	124 x 136 x 108	280	515 x 280 x 125	2.5
GGSM3AA-2560R12	5908267914762	25	15.0 x 11.0 x 1.0	0.4	103 x 123 x 7	9.5	124 x 136 x 108	280	515 x 280 x 125	2.5