

PRODUCT-DETAILS

GRNY-125-9-C

GROMMETING EXTD .125IN NAT NYL100FT



General Information

Extended Product Type	GRNY-125-9-C
Product ID	7TAG009750R0031
EAN	5414363023654
Catalog Description	GROMMETING EXTD .125IN NAT NYL100FT
Long Description	Extruded Grommeting, Natural Nylon 6.6 for Temperatures up to 85 Degrees Celsius (185 F), Height of 5.58mm (0.220 Inches), Width of 5.21mm (0.205 Inches), Thickness 1.27mm (0.05 Inches), Width Maximum Panel Thickness of 3.17mm (0.125 Inches), 30.48m (100 Foot) Reel

Ordering

EAN	5414363023654
UPC	728494102269
Country of Origin	United States (US)
Customs Tariff Number	3926909985
Selling Unit of Measure	each

Dimensions

Product Net Depth / Length	100 ft
	30.48 m

Container Information

Package Level 1 Units	1 piece
-----------------------	---------

Package Level 1 Width	12 in 305 mm
Package Level 1 Height	2.13 in 54 mm
Package Level 1 Depth / Length	17 in 432 mm
Package Level 2 Units	10 piece
Package Level 2 Width	12.75 in 324 mm
Package Level 2 Height	14.75 in 375 mm
Package Level 2 Depth / Length	18.25 in 464 mm

Additional Information

Brand / Label	Ty-Rap
Color	Natural
Effective Date	19960215
Material	Nylon/Polyamide 6.6
Panel Thickness	0.125 in 3.17 mm
Product Name	NYLON GROMMETING
Product Type	Grommeting
Special Functions	Used to line panel edges and knockouts where the chafing of wires is a concern
Sub Brand / Label	Catamount

Certificates and Declarations (Document Number)

Data Sheet, Technical Information	GRNY-125-9-C
Instructions and Manuals	GRNY-125-9-C

Classifications

ETIM 6	EC002604 - Cable bundle hose
ETIM 7	EC002604 - Cable bundle hose
ETIM 8	EC002604 - Cable bundle hose
UNSPSC	39131603
WEEE Category	Product Not in WEEE Scope
IDEA Granular Category Code (IGCC)	5393 >> Grommet edging

Categories

Low Voltage Products and Systems → Installation Products → Wire Management and Connectivity → Cable Ties

