




A
B

Transfer or duplication of this document as well as the utilisation or communication of its content are not permitted unless express consent is granted. Violations give rise to claims for damages. All rights reserved in case of patent, utility model or design patent registrations. Tolerance specifications do not include clearances inherent in the design.

Weitergabe sowie Vervielfältigung dieses Dokuments, Verwertung und Mitteilung seines Inhalts sind verboten, soweit nicht ausdrücklich gestattet. Zuwiderhandlungen verpflichten zu Schadenersatz. Alle Rechte für den Fall der Patent-, Gebrauchsmuster- oder Designeintragung vorbehalten. Bauartbedingtes Spiel ist in den Toleranzangaben nicht berücksichtigt.



- General Information:
- Simplified representation, exemplary shown in gray.
 - Tolerances apply in a normal climate according to DIN EN ISO 291-23/50-2, PA plastic parts with about 2% (% by weight) moisture content.
 - Workpiece zero point for mechanical processing
 - Tolerances for printing DIN ISO 2768-m
 - Web: www.phoenixcontact.com webcode: #1635
- Additional Information:
- A. Mounting rail like EN 60715, TH 35-7,5 or mounting rail similar to EN 60715, TH 35-15x1,5
 - B. PCB t=1,6±0,2
 - C. Guidance slot for TBUS8 . . .
 - D. Opening for fixing ICS25-C100 . . . or ICS25-TL100 . . .
 - E. Notch for locking release, by screw driver
 - F. Opening for ICS-FE-CONTACT
 - G. Fixing PCB
 - H. Guidance for ICS25-F . . . or ICC25 . . .
 - I. PCB guidance
 - J. Max. marking area left, with standard printing process, other printing processes on request.
 - K. Max. marking area right, with standard printing process, other printing processes on request.

Pos.	QTY	Description	Material
1	1	BOTTOM PART	PA
2	1	FOOT CATCH	STL
3	1	SPRING	STL

DIN A2

PHOENIX CONTACT

document-no. / ri

01067039 / 02

article-no.

2203884

date

29.08.2024

document-type

TECDOC 2D_Productdrawing

description

ICS25-B100X120-V-7035

scale

1:1

- Simplified representation
- Document excluded from change process
- Linear dimensions [mm]

page 1

of 1