

DC Barrel Jack Adapter DC 5.5 x 2.5 mm female to female with thread straight

Description

The DC adapter by Delock is suitable for reliable power supplies and for screw mounting on devices, panels or simply as a cable coupling. DC connectors can be connected both with and without union nut.



DC 5.5 x 2.5 mm

Item no. 90940

EAN: 4043619909407

Country of origin: China

Package: Zip poly bag

Technical details

- Connectors:
 - 1 x DC 5.5 x 2.5 mm female
 - 1 x DC 5.5 x 2.5 mm female
- Current: max. 5 A
- Operating voltage: max. 24 V
- Colour: black
- Shape: hexagon
- Version: straight
- Thread length: 9 mm
- Thread type: M8*P0.75
- Housing material: PVC
- Operating temperature: -40 °C ~ 80 °C
- Dimensions (LxD): ca. 58 x 14 mm

Package content

- DC barrel jack adapter
- 2 x nut
- 2 x serrated lock washer

Images



Panel cutout



Areas of application



General

Mounting type:	Screw mounting
Style:	straight both sides identical

Interface

Connector 1:	1 x DC 5.5 x 2.5 mm female
Connector 2:	1 x DC 5.5 x 2.5 mm female

Technical characteristics

Operating voltage:	24 V
Operating temperature:	-40 °C ~ 80 °C
Maximum current:	10 A

Physical characteristics

Housing material:	PVC
Thread length:	9 mm
Cable gauge:	22 AWG
Screw type:	Screw interface: M8 x 0.75
Diameter:	14 mm
Length:	58 mm
Colour:	black
Insulator:	PVC

Manufacturer information

Street	Beeskowdamm 13/15
Postal code	14167
City	Berlin
Country	Deutschland
E-Mail	info@delock.de
Website	www.delock.de