

HDMI KVM Switch 4K 60 Hz with USB 5 Gbps and Audio

Description

This KVM switch by Delock is a convenient solution for connecting **four computers** with HDMI output to **one HDMI monitor**.

Peripheral devices

Furthermore, two USB 2.0 ports for a mouse and keyboard, and **two USB 5 Gbps ports** for a hard drive or USB memory can be connected.

Flexible Control

The active computer can be selected by mouse gesture, keyboard hotkey, button on the device or infrared remote control.

Please Note

KVMs emulate a standard wired 104 key keyboard and wired generic 2 or 3 button scroll wheel mouse on their respective console ports. Whether or not a wireless or gaming mouse and keyboard work with KVM switches depends on several factors; in general, most wireless mice and keyboards do not support working with KVM switches. We recommend to use a standard wired mouse and keyboard with our KVM switches.



Item no. 11483

EAN: 4043619114832

Country of origin: China

Package: Retail Box

Technical details

- Connectors:
 - Input:
 - 4 x HDMI-A female
 - 4 x USB 5 Gbps Type-B female
 - 8 x 3.5 mm 3 pin stereo jack female (audio)
 - 1 x 3.5 mm 3 pin stereo jack female for optional IR-receiver
 - 1 x DC 5 V power connector screwable
 - Output:
 - 1 x HDMI-A female
 - 2 x USB 5 Gbps Type-A female (USB Hub)
 - 2 x USB 2.0 Type-A female (keyboard + mouse)
 - 4 x 3.5 mm 3 pin stereo jack female (audio)
- Switching via button, mouse button, hotkey or infrared remote control
- Automatic switching when turning a PC on or off
- Supports HDCP 1.4 and 2.2

- Supports HDR
- HDMI output:
Resolution up to 3840 x 2160 @ 60 Hz (depending on the system and the connected hardware)
- Robust metal housing
- Colour: black
- Dimensions (LxWxH): ca. 243 x 75 x 26 mm

Power supply specification

- Wall power supply
- Input: AC 100 ~ 240 V / 50 ~ 60 Hz / 0.6 A
- Output: 5.0 V / 3.0 A / 15.0 W
- Ground outside, plus inside
- Dimensions:
inside: ø ca. 2.1 mm
outside: ø ca. 5.5 mm

System requirements

- PC with HDMI female + USB Type-A female
- Monitor or TV with HDMI connector
- Connection cable

Package content

- KVM switch with USB and audio
- Infrared remote control
- 4 x cable USB 5 Gbps A male to USB 5 Gbps B male, length ca. 1.0 m
- External power supply
- Mounting brackets and screws
- User manual

Images



Interface

Output:	4 x 3.5 mm stereo jack female (speaker, microphone) 1 x HDMI-A female 2 x USB 5 Gbps Type-A female 2 x USB 2.0 Type-A female
Input:	4 x 3.5 mm stereo jack female (speaker, microphone) 2 x HDMI-A female 1 x 5 V DC female 5,5 mm x 2,1 mm 2 x USB 5 Gbps Type-B female

Technical characteristics

Maximum screen resolution:	3840 x 2160 @ 60 Hz
----------------------------	---------------------

Physical characteristics

Housing colour:	black
Housing material:	metal
Length:	178.0 mm
Width:	75 mm
Height:	26 mm

Manufacturer information

Street	Beeskowdamm 13/15
Postal code	14167
City	Berlin
Country	Deutschland
E-Mail	info@delock.de
Website	www.delock.de