

Delock ISM 433 MHz Antenna SMA 2.5 dBi Omnidirectional Flexible Rubber Black

Description

Use this antenna to devices with SMA connector to the ISM frequency band to receive and transmit 433 MHz signals. The flexible design makes this antenna resistant to impacts.



Item no. 88914

EAN: 4043619889143

Country of origin: China

Package: Zip poly bag

Technical details

- SMA plug
- Frequency range: 433 MHz
- Gain: 2,5 dBi
- Polarisation linear vertical
- Impedance: 50 Ohm
- Operating temperature: -10 °C ~ 75 °C
- Antenna length: 10.80 cm
- Diameter: SMA 8 mm

Package content

- Antenna

Interface

Connector:	1 x SMA plug
------------	--------------

Technical characteristics

Frequency range:	433 MHz
Antenna gain:	2.5 dBi
Impedance:	50 Ω
Operating temperature:	-10 °C ~ 75 °C
Polarisation:	vertical linear
VSWR:	< 2.0

Physical characteristics

Antenna type:	omnidirectional
Length:	108 mm
Diameter connector:	8.0 mm
Colour:	black

Manufacturer information

Street	Beeskowdamm 13/15
Postal code	14167
City	Berlin
Country	Deutschland
E-Mail	info@delock.de
Website	www.delock.de

