

DisplayPort 1.2 extension cable 4K 60 Hz 5 m

Description

This DisplayPort cable by Delock enables the extension of a DisplayPort connection. The triple shielded cable supports a resolution of up to Ultra HD (4K @ 60 Hz) and is downwards compatible to Full-HD 1080p.



Item no. 80004

EAN: 4043619800049

Country of origin: China

Package: Retail Box

Technical details

- Connectors:
1 x DisplayPort male
1 x DisplayPort female
- DisplayPort 1.2 specification
- Pin 20 is connected (supports 3.3 V)
- Cable gauge: 26 AWG
- Cable diameter: ca. 8.5 mm
- Copper conductor
- Triple shielded cable
- Contacts gold-plated
- Transmission of audio and video signals
- Data transfer rate up to 21.6 Gbps
- Resolution up to 3840 x 2160 @ 60 Hz
(depending on the system and the connected hardware)
- Colour: black
- Length incl. connectors: ca. 5 m

System requirements

- A free DisplayPort interface

Package content

- DisplayPort cable

Images



Interface

Connector 1:	1 x DisplayPort male
Connector 2:	1 x DisplayPort female

Technical characteristics

Data transfer rate:	21.6 Gbps
Maximum screen resolution:	3840 x 2160 @ 60 Hz

Physical characteristics

Cable gauge:	28 AWG
Length:	5 m
Colour:	black

Manufacturer information

Street	Beeskowdamm 13/15
Postal code	14167
City	Berlin
Country	Deutschland
E-Mail	info@delock.de
Website	www.delock.de