

PoweredUSB extension cable 24 V 2 m

Description

This cable by Delock allows the extension of a PoweredUSB connection and can be used to connect various devices. The cable is used both for data transmission and for power supply of the connected device.



Item no. 85986

EAN: 4043619859863

Country of origin: China

Package: Zip poly bag

Technical details

- Connectors:
 - 1 x PoweredUSB male 24 V >
 - 1 x PoweredUSB female 24 V
- PoweredUSB specification
- Voltage: 24 V
- Cable gauge:
 - 26 AWG data line
 - 20 AWG power line
- Cable diameter: ca. 6.5 mm
- Cable double shielded
- Colour: black
- Length incl. connectors: ca. 2 m

System requirements

- PC or hub with a free PoweredUSB 24 V female port

Package content

- PoweredUSB cable

Images



Interface

Connector 1:	1 x PoweredUSB male 24 V
Connector 2:	1 x PoweredUSB female 24 V

Technical characteristics

Voltage:	24 V
----------	------

Physical characteristics

Cable gauge:	26 AWG data line 20 AWG power line
Length:	2 m
Colour:	black

Manufacturer information

Street	Beeskowdamm 13/15
Postal code	14167
City	Berlin
Country	Deutschland
E-Mail	info@delock.de
Website	www.delock.de