

MS-D1ST-01

Full-motion touchscreen desk stand

- Position your screen perfectly for an optimal ergonomic position
- Designed for touch screen monitors: provides a flexible and stable platform for drawing, illustrating, reading, etc.



Features

- Height adjustable monitor desk stand
- Easy stepless height adjustment between 75 325 mm
- Swivel base and free-tilting design enable easy screen adjustments for better viewing angles and reduced glare
- Works with almost any LCD monitor (max. 32" / 10 kg)
- Stable base plate for secure placement on any desk
- Built-in cable management for an organized and neat workspace
- VESA compatible: Max. 100 x 100 mm

Packaging

Q'ty in crtn, pcs
Crtn volume, CUM
Crtn weight, kgs
Individual package size LxWxH:
Carton size LxWxH:
Country of origin
Barcode
Customs code

4
0.0615
19.58
395x115x290 mm
600x410x250 mm
CN
8716309135221
8302500000

Package contents

Monitor stand
User manual

Specifications

Material: aluminum, steel, plastic
Surface finish: powder coating
Color: Matte black
FSupported screen size: 17" 32"
Weight capacity: 2 ~ 10 kg
VESA compatible: 75 x 75, 100 x 100 mm
Height adjustment: 265 ~ 415 mm
Tilt range: +90 ° ~ -90 °
Swivel range: +40 ° ~ -40 °
Screen Rotation: +180 ° ~ -180 °
Net weight: 3.96 kg
Dimensions: 325 x 306 x 382 mm

Certificates

