

▶ ACOUSTIC-OPTICAL
SIGNALING DEVICE
SAO-Wd2



▶ **Technical data:** _____

Type	acoustic-optical
Supply voltage	10..18 V DC
Current consumption at 12 V DC	<150 mA
Power consumption at 12 V DC	<1,8 W
Working temperature range	-10°C ÷ +55°C
Sound output at 1m	>90 dB
Light colour	orange
Number of flashes [s ⁻¹]	~ 1 Hz
Flash time	~ 0,45 s
Max cross section	2,5 mm ²
Housing	plastic
Housing colour	white base, white body, orange shade
Ingress protection	IP21C
Mounting	wall/ceiling
Working environment	indoors
Dimensions	ø115x76 mm
Weight	~190 g

▶ **Product description:** _____

- The alarm generates acoustic and optical signals.
- Orange optical signal.
- Alarm signal generated after connecting power supply.
- Compact design.

▶ **Connection diagram:** _____

