

Product Datasheet

Item No.: 812887

as
Schwabe
TechnikProdukte

PRODUCT NAME

Cable reel for working at heights 40 m H07RN-F 3G2,5 IP44 "F"



Made in Germany

- Reel body made from robust, shatter-proof special plastic with cable reel
- With stable, shock-absorbing and galvanized single-foot frame with parking brake
- Frame with ergonomically shaped handle and cable guide
- With built-in thermal circuit breaker
- Connector for shock-proof plugs with lockable safety cover
- With 1.5 m power cord with shock-proof plug
- Cable in red signal color
- IP44: protected against foreign bodies and splash-proof
- 230 V, 16 A, max. 3,500 W

Reference image

Technical data

EAN	4059948001880
Weight [kg]	9.75
Dimensions	21x42x32 cm
Main color	black
Category	Cable reels
Subcategory	Extension reels for Outdoor Use
Cable type	H07RN-F
Cross section [mm ²]	3G2,5
Cable color	black
Cable length [m]	40
Rated voltage [V]	230
Rated current [A]	16
Maximum power	3500 W
Brake	Yes
Drum diameter	320 mmØ
Metal frame	Yes
Thermal fuse	1P
IP protection	IP44
Input	Shock-proof plug 230 V, 16 A, IP44 with 40 m H07RN-F 3G2,5
Output	1x shock-proof connector with black cover 230 V, 16 A, IP44 "F"
Total number of sockets	1
Number of Type E sockets (230 V)	1
Number of cores	3

Your partner for professional lighting and electrical products.