

WLAN 802.11 ac/a/h/b/g/n Antenna N jack 6 - 8 dBi 28 cm omnidirectional fixed pole mount white outdoor

Description

This WLAN antenna by Delock allows the usage of different WLAN bands outside.



Item no. 89440

EAN: 4043619894406

Country of origin: Taiwan,
Republic of China

Package: Poly bag

Technical details

- Connector: 1 x N jack
- Frequency range:
2.4000 - 2.4835 GHz
5.1500 - 5.8750 GHz
- Antenna gain: 6 - 8 dBi
- Impedance: 50 Ohm
- VSWR: 1.5
- Polarisation: vertical
- HBW horizontal beamwidth: 360°
- VBW vertical beamwidth: 23°
- Transmission power: max. 100 W
- Operating temperature: -40 °C ~ 80 °C
- Housing material: GFRP
- Colour: white
- Weight: ca. 120 g
- Dimensions (LxD): ca. 282 x 22.5 mm


System requirements

- Device with one free N port

Package content

- Antenna
- Pole mounting kit

Images



General

Mounting type:	pole
Suitable for outdoor:	yes

Interface

Connector:	1 x N female
------------	--------------

Technical characteristics

Frequency range:	2.4000 GHz - 2.4835 GHz 5.1500 - 5,8750 GHz
Antenna gain:	6 - 8 dBi
Beam width horizontal:	360°
Beam width vertical:	23°
Operating temperature:	-40 °C ~ 80 °C
Polarisation:	vertical
Transmission power:	max. 100 W
VSWR:	1.5

Physical characteristics

Antenna type:	omnidirectional Rod antenna
Housing material:	GFRP
Weight:	120 g
Dimensions (LxD):	282.0 x 22.5 mm

Manufacturer information

Street	Beeskowdamm 13/15
Postal code	14167
City	Berlin
Country	Deutschland
E-Mail	info@delock.de

Website

www.delock.de

