





5	6	7	8
REV.	ECN NO.	DATE	SIGN
DESCRIPTION			




PCB Layout

1	Red	紅	+
3	Black	黑	-
Conn.2	Wire Color	Conn.1	
Pin Out			




Note:

- * @@ Important Dimensions.
- * Waterproof Rate: Combine IP66
- * Power Jack: $\phi 3.5\text{mm}$
- * Cable: UL2464 24AWG*2C+D+AL,Black UV Resistant,OD=4.2 mm
- * Maximum Panel Thickness: 3.5mm
- * Gasket:Black,EPDM
- * Nut:Black,Nylon+GF



Pin Assignments



Recommended Panel Cut-Out

UNIT:mm		TITLE	
TOLERANCE		DC Power Jack Quick Type	
.X	±0.25	SCALE	Free
.XX	±0.1	SHEET	1 OF 1
.XXX	±0.05	REV.	A
ANGLES	±1°	SIZE	A4
		QC :Inspection Item	

LTW
亮泰企業股份有限公司

ITEM NO	LTWDCP-14RMFP-QC6001	DRAWN BY	EZ	DATE	2007/07/26
DWG NO	LTWDCP-14RMFP-QC6001	CHECKED BY	Jerry	DATE	2007/07/26
CUSTOMER		APPROVED BY	Victor Hung	DATE	2007/07/26