

MILAN S.r.l. a socio Unico
Head Office - Export Department
 Viale Europa, 74
 20047 Cusago (MI) Italy
 Tel. +39 02 9039.4556 - 4158
www.taskercables.com

Ufficio Commerciale e Distribuzione
 Viale Europa, 72 Strada FI2
 20047 Cusago (MI) Italy
 Tel. +39 02 9039.0037 - 0059
www.tasker.it

Capitale Sociale € 100.000,00 i.v.
 Cad. Fisc. e RIVA/VAT Nr. IT 03835660154
 RE.A. MI 975732 Reg. Imprese MI 178864-5179-14
 PEC: taskerpec@legalmail.it

Technical Datasheet

tasker® C286 Balanced Microphone Cable



CATEGORY APPLICATIONS

Balanced Microphone Cable (See Audio Catalogue)
 Premade Audio Cables, Microphones and Audio Multiline.

- A:** Soft Flame Retardant PVC sheath. Available in different colors.
 Outer Diam. Ø 3,80 ($\pm 0,20$) mm.
- B:** Shielding in O.F.C. red copper Spiral covering 100% +
 O.F.C. Tinned copper Drain Wire.
- C:** The cores are stranded in a pair with waste filler between conductors
 and wrapped with not woven polyester based tape.
 Core Insulation with a compact XLPE, colored one Red and one
 Transparent. Diam. Ø 1,20 ($\pm 0,20$) mm.
- D:** O.F.C. red copper formation 28x0,10 mm.
 Nom. Cross section 2x0,22 mm².

MARKING

tasker® C286 - 2x0,22 mm² - O.F.C. LOW CAPACITANCE

MULTILINE AUDIO CABLE - FirestoP® - Made In Italy

C286 LSZH

AVAILABLE ALSO CUSTOM PRODUCTION

This product may be custom produced also in **PE** or **PUR** and in all
 versions with Metallic Armor.

Cable Properties

Conductor Resistance	79,15 Ω/Km
Capacity Core/Core	70 pF/m
Capacity Core/Shield	160 pF/m
Max Rated Voltage	49 V
Operative Temperature	-20/+70°C

USE	X	Indoor	Interno Edificio
Impiego		Outdoor Limited	Esterno Limitato
		Outdoor	Esterno
		Outdoor Direct Burial	Esterno Interrato

INSTALLATION	X	Fixed	Fissa
Posa	X	Restricted Mobile	Mobile Limitata
		Mobile	Mobile
		Mobile in Drag Chain	Mobile in Catena

INFORMATION	X	RoHS2 Compliant
Informazioni	X	Ver. B / 19.12.25