

# Antenna base M6 with connection cable RG-58 C/U 3 m SMA plug black

## Description

This antenna mounting base by Delock enables antenna mounting, e.g. on a vehicle roof.



**Item no. 12589**

EAN: 4043619125890

Country of origin: China

Package: Box

## Technical details

- Connector:
  - 1 x M6 outer thread
  - 1 x SMA plug
- Impedance: 50 Ohm
- Mounting type: screw mounting
- Diameter mounting hole: ca. 11,0 mm
- Suitable for material thicknesses: 0 - 3 mm
- Operating temperature: -30 °C ~ 70 °C
- Housing material: ABS
- Colour: black
- Thread type: M6
- Thread length: ca. 7 mm

## System requirements

- Metallic mounting surface (e.g. vehicle roof)

## Package content

-

## General

|                       |                |
|-----------------------|----------------|
| Mounting type:        | Screw mounting |
| Suitable for indoor:  | yes            |
| Suitable for outdoor: | yes            |

## Interface

|              |              |
|--------------|--------------|
| Connector 1: | 1 x SMA plug |
|--------------|--------------|

## Physical characteristics

|                    |                          |
|--------------------|--------------------------|
| Thread length:     | 7 mm                     |
| Cable category:    | coaxial                  |
| Cable attenuation: | 0.6 dB @ 1 GHz per meter |
| Cable colour:      | black                    |
| Cable length:      | 3 m                      |
| Diameter:          | 44.5 mm                  |
| Height:            | 32 mm                    |
| Thread type:       | M6                       |
| Cable diameter:    | 4.95 mm                  |

## Manufacturer information

|             |                   |
|-------------|-------------------|
| Street      | Beeskowdamm 13/15 |
| Postal code | 14167             |
| City        | Berlin            |
| Country     | Deutschland       |
| E-Mail      | info@delock.de    |
| Website     | www.delock.de     |

