

RJ45 Network Cable Cat.8.1 S/FTP 0.5 m up to 40 Gbps black

Description

This network cable by Delock can be used to connect various devices and is suitable for 40GBASE-T Ethernet applications with a frequency of 2 GHz and a data transfer rate of up to 40 Gbps.



Item no. 80570

EAN: 4043619805709

Country of origin: China

Package: Zip poly bag

Technical details

- Connectors:
 - 1 x RJ45 plug
 - 1 x RJ45 plug
- Cat.8.1 specification
- Data transfer rate up to 40 Gbps
- Shielded (S/FTP)
- Pair in metal foil (PiMF)
- Cable gauge: 26 AWG
- Environmental temperature: -20 °C ~ 75 °C
- Cable diameter: ca. 6.0 mm
- Colour: black
- Material: TPE / LSZH (halogen-free)
- Length incl. connectors: ca. 0.5 m

Package content

- Patch cable

Images



General

Specification:	Cat. 8.1
Style:	both sides identical

Interface

Connector 1:	1 x RJ45 male
Connector 2:	1 x RJ45 male

Technical characteristics

Data transfer rate:	40 Gbps
Storage temperature:	-20 °C ~ 75 °C

Physical characteristics

Cable gauge:	26 AWG
Material:	TPE-LSZH
Length:	0.5 m
Colour:	black
Cable diameter:	6 mm

Manufacturer information

Street	Beeskowdamm 13/15
Postal code	14167
City	Berlin
Country	Deutschland
E-Mail	info@delock.de
Website	www.delock.de