

Adapter DisplayPort 1.2 male > DVI female 4K Passive white

Description

This adapter by Delock enables the connection of a DVI monitor to the system via a free DisplayPort interface. The adapter supports a resolution up to 4K Ultra HD at 30 Hz and is backward compatible to Full-HD 1080p.



Item no. 62602

EAN: 4043619626021

Country of origin: China

Package: Retail Box

Technical details

- Connectors:
 - 1 x DisplayPort 20 pin male >
 - 1 x DVI 24+5 female with nuts
- Chipset: Parade PS8402A
- DVI-D (Single Link), VGA not wired
- DisplayPort 1.2 specification
- Passive converter (level shifter), suitable only for graphics cards with DP++ output
- Resolution:
 - DVI up to 1920 x 1080 @ 60 Hz
(depending on the system and the connected hardware)
 - HDMI with the help of an adapter cable up to 3840 x 2160 @ 30 Hz
(depending on the system and the connected hardware)
- Connectors: gold-plated
- 1 x ferrite core
- Cable length without connectors: ca. 20 cm
- Colour: black
- OS independent, no driver installation necessary

System requirements

- A free DisplayPort DP++ female

Package content

- Adapter DisplayPort to DVI

Images



General

Specification:	DisplayPort 1.2 HDCP 1.3
----------------	-----------------------------

Interface

Connector 1:	1 x DisplayPort male
Connector 2:	1 x DVI 24+5 female with nuts

Technical characteristics

Chipset:	Parade PS8402A
Maximum screen resolution:	1920 x 1080 @ 60 Hz

Physical characteristics

Ferrite core:	1 x
Cable length:	20 cm (without connector)
Colour:	white

Manufacturer information

Street	Beeskowdamm 13/15
Postal code	14167
City	Berlin
Country	Deutschland
E-Mail	info@delock.de
Website	www.delock.de