

UTP Cat6 Patch cord, 1.5 m, red

PP6U-1.5M/R



Features

- CAT6 stranded unshielded (UTP) patch cord, 8P8C
- Snagless boots

Specifications

Category: category 6
 Type: UTP (unshielded)
 Frequency bandwidth: Max. 250 MHz
 Compliance with ANSI / TIA / EIA-568B standards
 Conductor: AWG 26 (7 x 0.15 mm wire), CCA
 Conductor insulation: HDPE 0.85 mm
 Shielding: n/a
 LDPE filler: yes
 Polyester tape: n/a
 Drain wire: n/a
 Jacket material: PVC
 Jacket braiding: n/a
 Jacket outer diameter: 6.2 mm
 Length: conform item description
 Color: conform item description

Packaging

Q'ty in crtn, pcs	200
Crtn volume, CUM	0.037
Crtn weight, kgs	9.2
Individual package size LxWxH:	175x130x20 mm
Carton size LxWxH:	400x300x310 mm
Country of origin	CN
Barcode	8716309127004
Customs code	8544421000

Certificates

