


The reproduction and/or divulgation of this drawing or its included informations is strictly prohibited unless authorized by the owning company DUCATI S.p.A.
E' vietata la riproduzione e/o la divulgazione di questo disegno unitamente alle informazioni in esso contenute senza l'autorizzazione della DUCATI S.p.A.



Characteristics: Self healing metallized
polypropylene film, dry
sealed with resin.
Case and sealing cover
in self-extinguishing
plastic material.

Leads: Solid rigid annealed tinned
copper wire, nominal cross
section 0,5mmq insulated
with PVC, temperature
resistance 90°C, style H05 V2-U.

DUCATI part number: 416171306

Capacitance/Tolerance: 10 μ F $\pm 5\%$

Climatic category: -25/85/21

Operation classes and approvals: see marking

Reference standards: EN 60252-1/A1

Marking:



DUCATI
energia

416.17.13..

10 μ F $\pm 5\%$

425V~ 30000h/cl.A

475V~ 10000h/cl.B

500V~ 3000h/cl.C

-25/85/21 S0
50-60 Hz



EN 60252-1/A1

Ed.	Descrizione/Description						Data/Date	Firma/Sign.
MODIFICHE/REVISIONS								
DUCATI energia s.p.a.		TOLL. QUOTE LIBERE (TOLERANCE RATE) UNI-ISO 2768-m	TOLL. QUOTE LIBERE ANG. (ANG. TOLERANCE RATE)	SCALA/SCALE	DATA/DATE	FIRMA/DRAWN	VISTO/CHECKED	
					25/11/2016	Ciccola		
OGGETTO/PART NAME Dimensions for metallized polypropylene film capacitor for A.C. use.						CODICE/PART NR. 416171306		
EDIZ./EDIT.								