

MA-DA1P-02

Adjustable desk display mounting arm, 17"-32"

- Position your screen perfectly
- Lightweight and tilting design
- Pole-mounted for easy height adjustment



Features

- Monitor desk mount with single monitor arm
- Arm rotates, extends and retracts, tilts to change reading angles, and allows to rotate display from landscape-to-portrait mode, etc
- Enables easy ergonomic positioning for reduced strain
- Pole-mounted for easy height adjustment
- Works with almost any LCD monitor (max. 32")
- Durable adjustable gas-spring suitable for monitors up to 9 kg
- Built-in cable management for an organized and neat workspace

Packaging

Q'ty in crtn, pcs
Crtn volume, CUM
Crtn weight, kgs
Individual package size LxWxH:
Carton size LxWxH:
Country of origin
Barcode
Customs code

6
0.0316744
19.2
385x84x140 mm
400x289x274 mm
CN
8716309135344
8302500000

Package contents

Desk arm
User manual
Mounting tools bag

Specifications

Material: Steel, plastic
Surface finish: Electrophoresis, Powder Coating
Color: fine texture black
Supported screen size: 17" 32"
Weight capacity (per screen): 2 ~ 9 kg
VESA compatible: 75x75, 100x100 mm
Tilt range: +90° -90°
Swivel range: +90° ~ -90°
Screen rotation: +180° ~ -180°
Installation: grommet, clamp
Suggested desktop thickness: clamp: 10 ~ 80 mm, grommet: 10 ~ 40 mm
Cable management: yes

Certificates

