

USB 2.0 Cable USB Type-C™ male to male with magnetic textile jacket PD 3.0 60 W 2 m

Description

This USB cable by Delock enables the connection between a device with a USB Type-C™ connector and a PC or a laptop equipped with a free USB Type-C™ port. Supporting the USB Power Delivery standard, connected devices can be powered up to 60 W (20 V / 3 A).

Magnetic function

Due to the integrated magnets in the cable sheath the cable is tangle-free. The cable is automatically returned to a rolled-up position and always looks tidy.



Item no. 81120

EAN: 4043619811205

Country of origin: China

Package: Zip poly bag

Technical details

- Connectors:
 - 1 x USB 2.0 Type-C™ male
 - 1 x USB 2.0 Type-C™ male
- Cable gauge:
 - 30 AWG data line
 - 22 AWG power line
- USB Power Delivery (USB PD 3.0) support up to 60 watt (20 V / 3 A)
- Cable diameter: ca. 4.5 mm
- Data transfer rate up to 480 Mbps
- Cable with magnetic textile shielding
- Connector with metal housing
- Colour: black
- Length: ca. 2 m

Package content

- USB 2.0 cable

Images



General

Specification:	USB 2.0 USB Type-C™
Style:	both sides identical

Interface

Connector 1:	1 x USB 2.0 Type-C™ male
Connector 2:	1 x USB 2.0 Type-C™ male

Technical characteristics

Data transfer rate:	480 Mbps
Maximum current:	3 A

Physical characteristics

Cable gauge:	30 AWG data line 22 AWG power line
Length:	2 m
Colour:	black

Manufacturer information

Street	Beeskowdamm 13/15
Postal code	14167
City	Berlin
Country	Deutschland
E-Mail	info@delock.de
Website	www.delock.de