

Cable DisplayPort 1.2 male > DisplayPort male 4K 60 Hz 7 m

Description

This DisplayPort cable by Delock can be used to connect devices with DisplayPort interface, e.g. displays, projectors or TVs, to a PC or laptop. The triple shielded cable supports a resolution of up to Ultra HD (4K @ 60 Hz) and is downwards compatible to Full-HD 1080p.



Item no. 84861

EAN: 4043619848614

Country of origin: China

Package: Zip poly bag

Technical details

- Connectors:
 - 1 x DisplayPort 20 pin male >
 - 1 x DisplayPort 20 pin male
- DisplayPort 1.2 specification
- Pin 20 not connected
- Cable gauge:
 - 28 AWG power line
 - 30 AWG data line
- Cable diameter: ca. 7.3 mm
- Copper conductor
- Triple shielded cable
- Gold-plated connectors
- Transfer of audio and video signals
- Data transfer rate up to 21.6 Gb/s
- Resolution up to 3840 x 2160 @ 60 Hz (depending on the system and the connected hardware)
- Colour: white
- Length incl. connectors: ca. 7 m

System requirements

- A free DisplayPort interface
-

Package content

- DisplayPort cable
-

Images



General

Specification:	DisplayPort 1.2
Style:	both sides identical

Interface

Connector 1:	1 x DisplayPort male
Connector 2:	1 x DisplayPort male

Technical characteristics

Data transfer rate:	21.6 Gbps
Maximum screen resolution:	3840 x 2160 @ 60 Hz

Physical characteristics

Pin finishing:	gold-plated
Conductor material:	copper
Cable gauge:	30 AWG data line 28 AWG power line
Shielding:	triple
Length:	7 m
Colour:	white
Cable diameter:	7.3 mm

Manufacturer information

Street	Beeskowdamm 13/15
Postal code	14167
City	Berlin
Country	Deutschland
E-Mail	info@delock.de
Website	www.delock.de