

Serial Cable D-Sub 15 female with screw 90° right angled to D-Sub 15 female with screw 90° right angled 1 m black

Description

This **serial cable** by Delock is suitable as a **connection cable** for various devices with **D-Sub 15 pin connector**.

With angled connector

The **angled plug connector** enables a **space-saving installation** in tight spaces behind appliances.



Item no. 80476

EAN: 4043619804764

Country of origin: China

Package: Zip poly bag

Special features

- With one screw

Technical details

- Connectors: 2 x D-Sub 15 female with screw 90° right angled
- Screw type: #4-40 UNC
- Cable gauge: 24 AWG
- Operating temperature: -10 °C ~ 80 °C
- Cable diameter: ca. 7.6 mm
- Cable length incl. connectors: ca. 1 m
- Material: PVC
- Colour: black

Package content

- Cable

Images



General

Style:	both sides identical
--------	----------------------

Interface

Connector:	2 x D-Sub 15 female with screw 90° right angled
------------	---

Technical characteristics

Operating temperature:	-10 °C ~ 80 °C
------------------------	----------------

Physical characteristics

Cable gauge:	24 AWG
Screw type:	#4-40 UNC
Material:	PVC
Length:	1 m
Colour:	black
Cable diameter:	7.6 mm

Manufacturer information

Street	Beeskowdamm 13/15
Postal code	14167
City	Berlin
Country	Deutschland
E-Mail	info@delock.de
Website	www.delock.de