

# RS-232 Cable Serial D-Sub 9 male to male with narrow plug housing 5 m

## Description

This serial cable by Delock is suitable as a **connection cable** for modem, printer, measuring instruments, converters, RS-232 hubs, patch panels etc.

### Mini D-Sub 9 connector

These cables fit on any RS-232 port, as the mini D-Sub 9 connectors (44 x 33.3 x 15 mm) are small and compact. In this way, RS-232 connections can be used directly adjacent to each other.



5 m

**Item no. 86576**

EAN: 4043619865765

Country of origin: China

Package: Zip poly bag

## Technical details

- Connectors:
  - 1 x serial D-Sub 9 male with screws >
  - 1 x serial D-Sub 9 male with screws
- Cable gauge: 28 AWG
- Pin assignment: 1:1
- Colour: black
- Insulator: PVC
- Screw type: #4-40 UNC
- Cable diameter: ca. 5 mm
- Cable length incl. connectors: ca. 5 m

## System requirements

- A free D-Sub 9 female

## Package content

- Cable

---

## Images



## General

|                |   |
|----------------|---|
| Specification: | RS-232 (EIA / TIA)                                      |
| Style:         | Connection cable<br>Mini Sub-D9<br>both sides identical |

## Interface

|              |                                     |
|--------------|-------------------------------------|
| Connector 1: | 1 x serial Sub-D 9 male with screws |
| Connector 2: | 1 x serial Sub-D 9 male with screws |

## Technical characteristics

|                      |  |
|----------------------|--|
| Data transfer rate:  | 921.6 Kbps                                 |
| Signal transmission: | TxD, RxD, RTS, CTS, DTR, DSR, DCD, RI, GND |

## Physical characteristics

|                                |  |
|--------------------------------|--|
| Cable type:                    | AWM Style 2464 28 AWG 80 °C 300 V VW-1 |
| Cable length incl. connectors: | 5 m                                    |
| Pin finishing:                 | gold-plated                            |
| Conductor material:            | Copper tinned                          |
| Cable gauge:                   | 28 AWG                                 |
| Screw type:                    | #4-40 UNC                              |
| Shielding:                     | Aluminum foil                          |
| Colour:                        | black                                  |
| Cable diameter:                | 5 mm                                   |
| Cable jacket material:         | PVC                                    |
| Safety of Flammability:        | VW-1                                   |

## Manufacturer information

Street                      Beeskowdamm 13/15  
Postal code                14167

|         |                |
|---------|----------------|
| City    | Berlin         |
| Country | Deutschland    |
| E-Mail  | info@delock.de |
| Website | www.delock.de  |