

TECHNICAL DATA

Producer	Qoltec
Input voltage	220 – 240 V
Output voltage	12V
Type of charging	9 step charging mode
Operating voltage	13.8-15.5V
Battery capacity	2Ah-220Ah
Charging time	Depending on battery capacity
Connector	Red + black crocodile type terminals
Cooling system	1 x Fan
Display	LCD
Protection	Reverse polarity protection Overvoltage protection Short-circuit protection Overcurrent protection Protection against overheating Low voltage protection
Protection against inverse polarity	Yes
Cable length	0.50m
Power cord length	0.63m
Functions	Battery repair function Power supply function Child lock function
Usage	Maintenance-free batteries: AGM GEL SLA EFB LiFePO4
OTHER PARAMETERS	
Colour	Black, blue
Material	ABS
Operating temperature	-30°C ~ +50°C
Dimensions (D/L x W x H)	55 x 150 x 88 mm
Package	Box
Package contents	1 x Charger 1 x Warranty card 1 x Operating instructions
Package depth / length [mm]	60
Package width [mm]	230
Package height [mm]	110
Net weight [kg]	0.523
Gross weight [kg]	0.573
Certificate	CE
Warranty	24 month
EAN code	5901878524962