Delock ISM 433 MHz Antenna SMA 2.5 dBi Omnidirectional Flexible Rubber Black

Opis

Use this antenna to devices with SMA connector to the ISM frequency band to receive and transmit 433 MHz signals. The flexible design makes this antenna resistant to impacts.



Numer artykułu 88914

EAN: 4043619889143

Kraj pochodzenia: China

Opakowanie: Torba na zamek błyskawiczny

Szczegóły techniczne

- SMA plug
- Frequency range: 433 MHz
- Gain: 2,5 dBi
- Polarisation linear vertical
- Impedance: 50 Ohm
- VSWR
- Operating temperature: -10 °C ~ 75 °C
- Antenna length: 10.80 cm
- Diameter: SMA 8 mm

Zawartość opakowania

- Antenna

Wszelkie pojawiające się tutaj nazwy i znaki należą do ich odpowiednich właścicieli. Błędy drukarskie, zmiany & pomyłki zastrzeżone. **© 2026 by Delock. Wszelkie prawa zastrzeżone.**

Interfejs

Złącze:	1 x męski SMA

Właściwości techniczne

Zakres częstoliwości:	433 MHz
Siła anteny:	2,5 dBi
Impedancja:	50 Ω
Temperatura robocza:	-10 °C ~ 75 °C
Polaryzacja:	vertikal linear
VSWR:	< 2,0

Właściwości fizyczne

Typ anteny:	wielokierunkowy
Długość:	108 mm
Średnica złącza:	8,0 mm
Kolor:	czarny

Manufacturer information

Ulica	Beeskowdamm 13/15
Kod pocztowy	14167
Miasto	Berlin
Kraj	Deutschland
Email	info@delock.de
Strona internetowa	www.delock.de

Wszelkie pojawiające się tutaj nazwy i znaki należą do ich odpowiednich właścicieli. Błędy drukarskie, zmiany & pomyłki zastrzeżone. **© 2026 by Delock. Wszelkie prawa zastrzeżone.**