


Antenna cable N Plug > RP-SMA Plug 90° RG-174 0.3 m

Description

The coaxial antenna cable by Delock allows the connection of radio frequency technology devices.



Item no. 89579

EAN: 4043619895793

Country of origin: Taiwan,
Republic of China

Package: Zip poly bag

Technical details

- Connectors:
 - 1 x N plug
 - 1 x RP-SMA plug 90°
- Impedance: 50 Ohm
- Cable: coaxial
- Cable type: RG-174
- Cable attenuation: 1 dB @ 1000 MHz per meter
- Cable diameter: ca. 2.70 mm
- Cable colour: black
- Smallest bending radius: ca. 1 cm
- Cable length incl. connectors: ca. 0.3 m

System requirements

- Device with free N or RP-SMA jack

Package content

- Antenna cable

Interface

Connector 1:	1 x N male
Connector 2:	1 x RP-SMA plug 90°

Technical characteristics

Impedance:	50 Ω
------------	------

Physical characteristics

Cable category:	coaxial
Cable type:	RG-174
Cable attenuation:	1 dB @ 1 GHz
Cable colour:	black
Cable length incl. connectors:	0.3 m
Pin finishing:	gold-plated nickel-plated
Smallest bending radius:	1 cm
Cable diameter:	2.7 mm

Manufacturer information

Street	Beeskowdamm 13/15
Postal code	14167
City	Berlin
Country	Deutschland
E-Mail	info@delock.de
Website	www.delock.de

