DL4 Solar Flat Cable male to female 1 m red

Description

This DL4 solar flat cable by Delock can be used to transmit power obtained from a photovoltaic system.

DL4 connectors

The DL4 plugs and sockets have a snap-in function, which avoids unwanted interruptions and ensures a secure connection. The connection can be released again with the appropriate tool.

IP67 dust and waterproof

The DL4 solar cable is protected from dirt and moisture.

Super flexible and flat

The solar flat cable is ideal for laying in a window bushing. The material of the cable sheath is flexible and makes the cable very resistant to strain.



Item no. 60676

EAN: 4043619606764

Country of origin: China

Package: Zip poly bag

Technical details

- Connectors:
  1 x DL4 male
  1 x DL4 female
- Cable cross section: ca. 3,3 mm²
- Compatible with MC4, TS4, QC4
- Operating temperature: -40 °C ~ 90 °C
- Cable size: ca. 10.0 x 2.0 mm
- Protection class: IP67
- Voltage: max. 1000 V
- Colour: red
- Length incl. connectors: ca. 1 m

System requirements

- A free DL4 port


Package content


All names and symbols mentioned here are property of the respective producer. Printing errors, changes and errors excepted. **© 2026 by Delock. All rights reserved.**

- DL4 cable

Images







All names and symbols mentioned here are property of the respective producer. Printing errors, changes and errors excepted. **© 2026 by Delock. All rights reserved.**

Interface

Connector 1:	1 x DL4 male
Connector 2:	1 x DL4 female

Technical characteristics

Voltage:	1000 V

Physical characteristics

Cable category:	Flat cable
Cable gauge:	12 AWG
Length:	1 m
Colour:	red

Manufacturer information

Street	Beeskowdamm 13/15
Postal code	14167
City	Berlin
Country	Deutschland
E-Mail	info@delock.de
Website	www.delock.de

All names and symbols mentioned here are property of the respective producer. Printing errors, changes and errors excepted. **© 2026 by Delock. All rights reserved.**