

THAR LED 7W A60, bulb with microwave motion sensor, 600lm, 4000K, E27

ViRONE

Marka: **Virone** | Symbol: **SW/MV-5** | Ean: **5908254824135**



PRODUCT DESCRIPTION

THAR LED a modern light source in shape of a bulb, equipped with SMD LED diodes, which guarantee high energy efficiency and long service life of the device. This product has rated power of 7W and emits light with luminous flux of 600lm. This product shines with a natural white color at a temperature of 4000K. Our LED bulb has a built-in microwave motion sensor, which allows to control other light source after motion is detected in the detection area, and when the ambient light is reduced to <20lux. The motion detection range is up to 10m. Lighting time, after detection of a motion is ca. 60 sec. The bulb has an E27 thread and does not require any

installation. Just install it in place of a standard bulb to automatically turn the lamp on and off.

TECHNICAL DATA

General information:

Nominal voltage [V]:	230
Lamp power [W]:	7
Voltage type:	AC
Luminous flux [lm]:	600
Colour rendering index CRI:	80-89
Lamp shape:	Kształt gruszki
Type of glass/cover:	Matowy
Colour of light according to EN 12464-1:	Neutralna 3300-5300 K
Socket:	E27
Colour:	Biały
Colour temperature [K]:	4000
Beam angle [°]:	360
Dimmable:	nie
Diameter [mm]:	60
Length [mm]:	108
Degree of protection (IP):	IP20
Energy efficiency class according to EU regulation 2019/2015:	F
Lamp designation:	Typ A
Weighted energy consumption in 1000 hours [kWh]:	7
Average nominal lifespan [h]:	25000
With movement sensor:	tak

