

Hot air tool - Professional Line

HM 2320 E

Folding box
EAN 4007841 089665
Article number 089665



series 5



Timer function

2300 W

2300 W Output

Display

Display (LCD)



80 - 650°C



stepless adjustable



150 - 500 l/min.



Suitable for
pluggable nozzles



VDE



CE

Function description

Powerhouse of energy saving. Sustainable working for the professional tradesman or industry. The 2300 W HeatMatic 2320 E provides absolute safety even with sensitive materials thanks to the display and the precise temperature setting of 80-650°C.

Technical specifications

Temperature	80 – 650 °C
Airflow rate	150 – 500 l/min
Temperature setting	in 10°C steps by joystick
Settings made via	joystick
Temperature display	LCD display
Airflow control	Settings
Programming function	Yes
Loc function	Yes
Residual heat indicator	Yes
Cool function	No
Motor, type	Brush motor
Heating element	Ceramic heating element
Mains power supply	220 – 230 V / 50 – 60 Hz

Function, hanger	Yes
Restart protection	Yes
Temperature scanner	Yes
Thermal cut-out	Yes
Thermostat	Yes
Nozzle receiver, type	34
Cord length	3 m
Dimensions (L x W x H)	253 x 87 x 200 mm
PU1, net weight	1,024 kg
Manufacturer's Warranty	1 year
PU1, EAN	4007841089665
Output	2300 W
Product category	Hot air tool

Accessories

EAN 4007841 014919

Temperature scanner HL Scan

EAN 4007841 053963

Hot Air Tool Guard Cage HL 1820 S - HG 2320 E

<https://www.steinell-tools.de/>

Subject to technical modifications

01.2026 Page 1 from 2

HM 2320 E

Folding box
EAN 4007841 089665
Article number 089665



Accessories

EAN 4007841 074616	Soldering reflector nozzle 10 mm
EAN 4007841 009571	Reduction nozzle
EAN 4007841 070618	Reduction nozzle
EAN 4007841 070717	Reduction nozzle
EAN 4007841 074715	Wide-slit nozzle
EAN 4007841 068035	Adapter nozzle
EAN 4007841 070311	Window nozzle
EAN 4007841 070410	Window nozzle
EAN 4007841 070113	Surface nozzle
EAN 4007841 070212	Surface nozzle
EAN 4007841 070519	Reflector nozzle
EAN 4007841 070915	Welding nozzle
EAN 4007841 074715	Wide-slit nozzle
EAN 4007841 074616	Soldering reflector nozzle 10 mm
EAN 4007841 087715	Flat angled nozzle 40x2 mm for discharge pipe bead
EAN 4007841 075569	12-piece hot-air accessory kit
EAN 4007841 078218	Fine dust filter HL 1920 E - HG 2320 E