

# DVI Cable 24+1 male to 24+1 male angled 1 m

## Description

This DVI cable by Delock can be used to connect a DVI monitor or a projector to the DVI interface of a PC or laptop.



**Item no. 85893**

EAN: 4043619858934

Country of origin: China

Package: Zip poly bag

## Technical details

- Connectors:
  - 1 x DVI 24+1 male >
  - 1 x DVI 24+1 male angled
- DVI-D (Dual Link)
- DVI connector with screws
- Cable gauge: 30 AWG
- Cable diameter: ca. 7.3 mm
- Copper conductor
- Contacts gold-plated
- Cable double shielded
- Data transfer rate up to 7.92 Gbps
- Resolution up to 2560 x 1600 @ 60 Hz  
(depending on the system and the connected hardware)
- Colour: black
- Length incl. connectors: ca. 1 m

## System requirements

- A free DVI interface

## Package content

- DVI cable

---

## Images



## General

Style:	angled 90° both sides identical
--------	------------------------------------

## Interface

Connector 1:	1 x DVI 24+1 male
Connector 2:	1 x DVI 24+1 male

## Technical characteristics

Data transfer rate:	7.92 Gbps
Maximum screen resolution:	2560 x 1600 @ 60 Hz
Maximum refresh rate:	60 Hz

## Physical characteristics

Pin finishing:	gold-plated
Conductor material:	copper
Cable gauge:	30 AWG
Length:	1 m
Colour:	black
Cable diameter:	7.3 mm

## Manufacturer information

---

Street	Beeskowdamm 13/15
Postal code	14167
City	Berlin
Country	Deutschland
E-Mail	info@delock.de
Website	www.delock.de