



530EREC

Product no.: 530EREC

Distance cutter copper wire to a length of 1.3 mm/.051 Inch



Special tool steel, width of tips with tank (receptacle)
5.3 mm (0.209 Inches)



ESD-safe



When ordering, please indicate the desired cutting
length (= F on diagram) between 0.6 and 1.5 mm.



source images

The Perfect Cut - Strong, sharp and precise, every time

Weller Erem™ Cutters are designed to be strong, durable and sharp, having the highest precision available. Manufactured with uncompromising Swiss quality and created for worldwide applications, including electronics assembly and healthcare, Weller Erem Cutters are built to last. Feel the difference with Weller Erem™ – the proven choice. Every time.

Type	Type of Cut	Cutting Capacity
Series 500 Medium mm 0,03 0,1 0,2 0,3 0,4 0,5 0,6 0,7 0,8 0,9 1,0 1,1 1,2 1,3 1,4 1,5 1,6 1,7 1,8 1,9 2,0 Inch .001 .003 .007 .011 .015 .019 .023 .027 .031 .035 .039 .043 .047 .051 .055 .059 .062 .066 .070 .074 .078		
	512N	Semi Flush
	512E	Semi Flush
	599T	Semi Flush / Carbide
	522N	Flush
	599E	Flush
	532N	Super Full Flush
	576TX1	Flush / Carbide
	503E	Flush
	503ETST 30°	Flush / Carbide
	504AE	Flush
	555E 35°	Flush
	572E 40°	Flush
	582E 45°	Flush
	593AE 30°	Flush
	575E 45°	Flush
	592E	Flush
	792E	Super Full Flush
	576TX	Flush / Carbide
	570E	Flush
	573E	Flush
		for vertical tip cutting





Technical Data

Length mm	120
Length of cutting edges mm	---
Head width mm	11
Head thickness mm	6
Head length mm	26
Max. cutting capability – hard wire mm	---
Weight in oz	2.448
Length of cutting edges Inches	---
Head width Inches	0.433
Head thickness Inches	0.236
Head length Inches	1.024
ESD-safe	on
Cut	Flush
Max. cutting capability – medium hardness mm	---
Max. cutting capability – copper wire mm	Ø 1,2
Length inches	4.724
Weight in g	69.4
Erem applications	---