

SuperSpeed USB Card Reader for SD / Micro SD / MS memory cards

Description

This card reader by Delock has **three memory card slots** and allows to read and write many different memory cards. The card reader can be connected to a PC or laptop via the USB Type-A interface.



Item no. 91757

EAN: 4043619917570

Country of origin: China

Package: Retail Box

Technical details

- Connectors:
 - 1 x SuperSpeed USB (USB 3.2 Gen 1) Type-A male >
 - 1 x SD / MMC slot
 - 1 x MS slot
 - 1 x Micro SD / M2 slot
- Data transfer rate up to:
 - SuperSpeed USB 5 Gbps,
 - Hi-Speed 480 Mbps,
 - Full-Speed 12 Mbps,
 - Low-Speed 1.5 Mbps
- Display two drive letters at the same time (SD and micro SD / M2 slots must be used separately)
- 1 x LED indicator
- Dimensions (LxWxH): ca. 69 x 19 x 11 mm
- Hot Swap, Plug & Play
- Supports following memory cards:
 - Slot 1**
 - SD, SD3.0 UHS-I, SD High Capacity (SDHC), SD Ultra, SDHC Ultra, SDXC, MMC-I, MMC-II, MMC 4.0, Mini SD, Mini SDHC, MMCmobile, RS-MMC, RS-MMC 4.0

Slot 2

MS, High Speed Memory Stick (HS-MS), MS Pro, MS Pro-HG, MS-Pro Duo, MS-HG, Memory Stick XC, MS Magic Gate, MS-Pro Magic Gate, MS-Duo, MS-Duo Magic Gate, MS Pro-HG Duo, MS-Duo, MS XC-Duo, MS XC-HG Duo

Slot 3

Micro SD, Micro SD3.0 UHS-I, Micro SD4.0 UHS-II, Micro SDHC, Micro SDXC, T-Flash, MMCmicro, MS Micro, MS-Pro Micro, MS-HG Micro, MS XC-HG Micro, M2

System requirements

- Chrome OS
- Linux Kernel 5.8 or above
- Mac OS 11.2.3 or above
- Windows 8.1/8.1-64/10/10-64/11
- PC or laptop with a free USB Type-A port

Package content

- USB Card Reader
- User manual

Images



General

Supported operating system:	Chrome OS Linux Kernel 5.8.0 or above Windows 10 32-Bit Windows 10 64-Bit Windows 8.1 32-Bit Windows 8.1 64-Bit Mac OS 11.2.3 or above
-----------------------------	--

Supported memory card:	Micro SD
	Micro SDHC
	Micro SDXC
	SD
	MS Micro
	SDHC
	SDXC
	Micro SD UHS-I
	Micro SD UHS-II
	RS-MMC
	MS
	MS Pro
	MS PRO-HG
	MS Duo
	MS Pro MagicGate
	MS PRO Duo
	MS PRO-HG Duo
	MS XC-HG Duo
	MS XC Duo
	MMC-I
	MMC-II
	MMC 4.0
	RS-MMC 4.0
	MS PRO-HG Micro
	M2
	MS MG Pro Duo
	HS MS Pro Duo
	SD 3.0 UHS-I
	SD Ultra
	SDHC Ultra
	Mini SD
	Mini SDHC
	Mini SDXC
	MMC Mobile

Interface

Connector 1:	1 x USB 5 Gbps Type-A male
Connector 2:	1 x MS slot 1 x Micro SD Slot 1 x SD slot

Technical characteristics

Data transfer rate:	5 Gbps
---------------------	--------

Manufacturer information

Street	Beeskowdamm 13/15
Postal code	14167
City	Berlin
Country	Deutschland
E-Mail	info@delock.de
Website	www.delock.de