

Active USB 10 Gbps extension cable USB Type-C™ 5 m

Description

This active USB cable by Delock can be used to extend a USB connection by 5 m. The cable has an additional DC power socket to which an optional power supply can be connected. This ensures optimum data transmission even when used with powerful devices such as a 2.5" hard drive.

Please Note

The cable cannot transmit video signals, so it is not suitable to connect a USB Type-C™ monitor.



Item no. 80028

EAN: 4043619800285

Country of origin: China

Package: Retail Box

Technical details

- Connectors:
 - 1 x USB 10 Gbps USB Type-C™ male
 - 1 x USB 10 Gbps USB Type-C™ female
 - 1 x DC jack
- Chipset: Prolific PL2586
- DC jack for optional power supply
- Cable gauge:
 - 30 AWG data line
 - 24 AWG power line
- Cable diameter: ca. 4.8 mm
- Data transfer rate up to 10 Gbps
- Output current:
 - 1.5 A without power supply
 - 2 A with power supply
- Output voltage: 5 V
- Colour: black
- Dimensions of housing (LxWxH): ca. 62.1 x 23.1 x 11.5 mm
- Length without connectors: ca. 5 m

Specification of power connector

- Input: 5 V / 2 A
- Ground outside, plus inside
- Dimensions:
 - inside: ø ca. 1.35 mm
 - outside: ø ca. 3.5 mm
 - length: ca. 9.65 mm

Package content

- USB extension cable

Images



General

Specification:	USB 10 Gbps
----------------	-------------

Interface

Connector 1:	1 x USB Type-C™ male
Connector 2:	1 x DC jack 1 x USB Type-C™ female

Technical characteristics

Chipset:	Prolific PL2586
Data transfer rate:	10 Gbps
Maximum current:	1.5 A 2 A
Voltage:	5 V

Physical characteristics

Cable gauge:	30 AWG data line 24 AWG power line
Length:	5 m
Cable diameter:	4.8 mm

Manufacturer information

Street	Beeskowdamm 13/15
Postal code	14167
City	Berlin
Country	Deutschland
E-Mail	info@delock.de
Website	www.delock.de