

Adapter DisplayPort 1.2 male > VGA female white

Description

This adapter by Delock enables the connection of a VGA monitor to the system via a free DisplayPort interface.



12 cm

Item no. 61766

EAN: 4043619617661

Country of origin: China

Package: Retail Box

Technical details

- Connectors:
 - 1 x DisplayPort 20 pin male >
 - 1 x VGA 15 pin female
- Chipset: Analogix ANX9833
- DisplayPort 1.2 specification
- Resolution up to WUXGA 1920 x 1200 @ 60 Hz (depending on the system and the connected hardware)
- Transfer of analogue video signals
- 1 x ferrite core
- Cable length without connectors: ca. 12 cm
- Colour: white
- OS independent, no driver installation necessary

System requirements

- A free DisplayPort female port

Package content

- Adapter DisplayPort to VGA

Images



General

Specification:	DisplayPort 1.2
----------------	-----------------

Interface

Connector 1:	1 x DisplayPort male
Connector 2:	1 x VGA female

Technical characteristics

Chipset:	Analogix ANX9833
Maximum screen resolution:	1920 x 1200 @ 60 Hz

Physical characteristics

Ferrite core:	1 x
Cable length:	12 cm
Colour:	white

Manufacturer information

Street	Beeskowdamm 13/15
Postal code	14167
City	Berlin
Country	Deutschland
E-Mail	info@delock.de
Website	www.delock.de