



1503E

Product no.: 1503E

Cutting head for 1500 BSF - tip cutter - angled head



The angled head provides for precise cuts at different working angles.



source images

The Perfect Cut - Strong, sharp and precise, every time

Weller Erem pneumatic side cutters are light and precise. Thanks to a selection of different cutting heads they can operate extremely versatile. The cutters are suitable for cutting conventional components, soft metals or small plastic parts. The cutting heads can be interchanged easily.

THE PERFECT CUT

Strong, sharp and precise - every time





Technical Data

Length mm	69.6
Length of cutting edges mm	11
Head width mm	10.5
Head thickness mm	6
Head length mm	20
Max. cutting capability – hard wire mm	---
Weight in oz	1.199
Length of cutting edges Inches	0.433
Head width Inches	0.413
Head thickness Inches	0.236
Head length Inches	0.787
ESD-safe	on
Cut	Flush
Max. cutting capability – medium hardness mm	1
Max. cutting capability – copper wire mm	1.6
Length inches	2.740
Weight in g	34
Erem applications	Microelectronic