

# USB Type-C™ Adapter to Gigabit LAN 10/100/1000 Mbps with Power Delivery port black

## Description

The adapter by Delock expands a PC or laptop by one **network interface via the USB Type-C™** interface. In addition, the adapter can also be operated on a Thunderbolt™ 3 interface.

### USB Power Delivery (USB PD 2.0) support up to 60 watt

The adapter has a USB Type-C™ Power Delivery port to connect the power supply of the laptop to charge it. The adapter can also be used without a power supply.



**Item no. 66644**

EAN: 4043619666447

Country of origin: China

Package: Retail Box

## Technical details

- Connectors:
  - 1 x USB 5 Gbps USB Type-C™ male
  - 1 x Gigabit LAN RJ45 jack
  - 1 x USB Type-C™ PD female (power supply)
- Chipset: Realtek RTL8153, VIA VL100
- Data transfer rate:
  - Ethernet up to 10 Mbps (Half/Full Duplex)
  - Fast Ethernet up to 100 Mbps (Half/Full Duplex)
  - Gigabit Ethernet up to 1000 Mbps (Half/Full Duplex)
- Compatible with:
  - IEEE 802.3: 10BASE-T
  - IEEE 802.3u: 100BASE-TX
  - IEEE 802.3ab: 1000BASE-T
- Supports Auto MDI-X (automatic detection of standard or crossover network cable)
- Supports Wake On LAN (WOL)
- Supports IEEE 802.3az (Energy Efficient Ethernet)
- Supports IEEE 802.1Q Virtual LAN (VLAN)
- Support full duplex operation with IEEE 802.3x flow control and half duplex operation with back-pressure flow control
- Supports 9k Jumbo Frames
- Output power for host: max. 60 W
- LED indicator for power and activity
- USB bus powered

- Colour: black
- Cable length incl. connectors: ca. 11.5 cm

---

## System requirements

- Android 9.0 or above
- Chrome OS 78.0 or above
- iPad Pro (2018)
- Linux Kernel 3.18 or above
- Mac OS 10.15.3 or above
- Windows 8.1/8.1-64/10/10-64/11
- Device with a free USB Type-C™ port or with a free Thunderbolt™ 3 port

---

## Package content

- USB Type-C™ Gigabit LAN adapter
- User manual

---

## Images



## General

Supported operating system:	Android 9.0 or above Chrome OS 78.0 or above Linux Kernel 3.18 or above Mac OS 10.15.3 or above Windows 10 32-Bit Windows 10 64-Bit Windows 8.1 32-Bit Windows 8.1 64-Bit iPad Pro (2018) Windows 11
LED indicator:	2 x

## Interface

Connector 1:	1 x USB 5 Gbps USB Type-C™ male
Connector 2:	1 x Gigabit LAN RJ45 jack
Connector 3:	1 x USB Type-C™ Power Delivery female

## Technical characteristics

Chipset:	Realtek RTL8153 VIA VL100
Data transfer rate:	Ethernet up to 10 Mbps Fast Ethernet up to 100 Mbps Gigabit Ethernet up to 1000 Mbps

## Physical characteristics

Colour:	black
---------	-------

## Manufacturer information

Street	Beeskowdamm 13/15
Postal code	14167
City	Berlin
Country	Deutschland
E-Mail	info@delock.de
Website	www.delock.de