

Eaton 63NHG01B

Catalog Number: 63NHG01B

Eaton Bussmann series low voltage NH Fuse, Live gripping lug, 500V, 63A, 120 kAIC, Combination fuse status indicator, Blade end connection, Class C gL/gG, Square-body with knife blade contact, Ceramic body

General specifications



Product Name	Catalog Number
Eaton Bussmann series low voltage NH Fuse	63NHG01B
	Packing Unit
	Case Pack
	Pack
EAN	Quantity
5027590363969	36
5027590203951	3
Gross Weight	Length
11.208 kg	325 mm
0.884 kg	137 mm
Width	Height
290 mm	155 mm
102 mm	68 mm
Volume	ERP Name
14608.75 cm ³	SAP-UNITY
950.232 cm ³	SAP-UNITY
Product Length/Depth	Product Height
135 mm	58 mm
Product Width	Product Weight
30 mm	270.667 g

Compliances

RoHS Compliant

Certifications

IEC 60269-1

Electrical data

Amperage Rating

63 A

Voltage rating

500 V

Voltage type

AC

Breaking capacity

120 kA

Frequency rating - min

45 Hz

Frequency rating - max

62 Hz

Product specification

DIN 43620

Fuse size

NH2

Insulated metal gripping lugs (IMGL)

No

Yes

Accessories

Suitable for

SD2-D Single pole NH Fuse base

TD2-D Tripe pole NH Fuse base

Microswitch 170H0235

Microswitch 170H0236

EBH Size 00 to 4 Horizontal fuse switch-disconnectors

Do pobrania



Eaton Corporation plc

Eaton House

30 Pembroke Road

Dublin 4, Ireland

Eaton.com

© 2024 Eaton. Wszelkie
prawa zastrzeżone.

Eaton is a registered trademark.

All other trademarks are
property of their respective
owners.



Eaton.com/socialmedia