



4513-SET-6

HSS-G Drill Bit Set for Metal - 6 Pcs



PRODUCT DETAILS

- Includes 6 drills from 2 mm to 8 mm x 1 mm (excluding 7 mm) in a plastic cassette
- 4411 HSS-G drill bits 2 mm, 3 mm, 4 mm, 5 mm, 6 mm, 8 mm
- Top angle of 130° with self-centring split-point tip for quick cutting and perfect centring
- Drill bits have a cylindrical shank (shank equal to drill bit diameter) and designed for use in drill stands and drill drivers
- High-speed steel (HSS) drill for drilling in bronze, brass, carbon steel, cast iron, alloy steel and stainless steel
- Manufactured to DIN 338 N
- Includes 6 drills from 2 mm to 8 mm x 1 mm (excluding 7 mm) in a plastic cassette
- High-speed steel (HSS) with ground flutes
- Long lasting performance
- Top angle 130°
- Split-Point
- Ground flutes enable fast drilling and high precision
- DIN 338N

PRODUCT ATTRIBUTES

Product		
4513-SET-6	6	150 g

Follow the Fish!



SET CONTENT



**HSS-G Drill Bit for Metal 2 mm x 49
mm**
4413-2.00



**HSS-G Drill Bit for Metal 3 mm x 61
mm**
4413-3.00



**HSS-G Drill Bit for Metal 4 mm x 75
mm**
4413-4.00



**HSS-G Drill Bit for Metal 5 mm x 86
mm**
4413-5.00





**HSS-G Drill Bit for Metal 6 mm x 93
mm**

4413-6.00



**HSS-G Drill Bit for Metal 8 mm x 117
mm**

4413-8.00

