


HOUSING LOWER PART





Assembly example


Overall dimensions complaint DIN 43880













FOOT CATCH



WALL MOUNTING




General Information:
- Tolerances apply in a normal climate according to DIN EN ISO 291-23/50-2
- Web: www.phoenixcontact.com

Additional Information:
A. PCB fixing
B. HBUS connector
C. PCB 1 (main PCB)
D. Housing upper part
E. Cover
F. Mounting rail like EN 60715: TH 35-7,5 or mounting rail TH 35-15x1,5 similar to EN 60715
G. Plug for HBUS, (PSTD 0,65x0,65/9-2,54)
H. Position PCB 9 or position plate

KIT (not mounted)			
Pos.	QTY	Description	Material
1	1	HOUSING LOWER PART	PC
2	2	FOOT CATCH	POM

HOUSING LOWER PART with FOOT CATCH not mounted



DIN A2	document-No. / RI: 00905813 / 03	date: 22.07.2025	scale: 1:1
PHOENIX CONTACT	ident.-No.: 2896254	document-type: TECDOC 2D_Productdrawing	
page 1 of 1	description: BC 35,6 UT HBUS BK		

Transfer or duplication of this document as well as the utilisation or communication of its content are not permitted unless express consent is granted. Violations give rise to claims for damages. All rights reserved in case of patent, utility model or design patent registrations.

Weitergabe sowie Vervielfältigung dieses Dokuments, Verwertung und Mitteilung seines Inhalts sind verboten, soweit nicht ausdrücklich gestattet. Zuwiderhandlungen verpflichten zu Schadenersatz. Alle Rechte für den Fall der Patent-, Gebrauchsmuster- oder Designeintragung vorbehalten.