

LogiLink®

USB-C Docking Hub 7-in-2 with Detachable Adapters For MacBook

Art. No.: **UA0482**

Expand. Connect. Charge!

Expand your MacBook with one powerful USB-C hub. Connect projectors, 4K displays, memory cards, USB drives, and more, while enjoying up to 100 W pass-through charging. The detachable modular design offers greater flexibility, allowing you to connect and use up to three devices simultaneously.



- 3 Detachable Modules
- 100W PD
- 4K UHD
- 5 Gbps Data Transfer
- SD microSD Supported
- LED Indicator
- Aluminum
- Portable
- Plug & Play

7-in-2 Expansions



One Hub, Three Ways to Connect

Use all three modules together as one powerful hub, or detach them to connect up to three different devices independently.



*The specifications and pictures are subject to change without prior notice.
*All trade names referenced are the registered trademarks of their respective owners.

UA0482

4 052792 086539

Made in China



Crystal Clear and Simultaneous Video Outputs

Bring your content to the big screen with smooth, detailed 4K/60 Hz HDMI output for work, entertainment, and presentations.

*MST function only works for Windows and Mac OS.



Fast, Flexible Memory Expansion

Read and write with ease using SD 3.0 and microSD cards. Supporting capacities up to 2 TB and high-speed standards such as UHS-I and eMMC 4.5 HS200, it makes transferring and managing large files quick and convenient.



100 W Power Delivery

Supports up to 100 W USB-C Power Delivery input while keeping your Mac-Book's charging port free for other uses.

*Proper use of the PD function can only be guaranteed in combination with certified USB cables with E-Mark chipset.



Wide Compatibility

Plug-and-play operation with macOS, Windows, ChromeOS, Linux and iPadOS.

Specification:

Input	2x USB-C male, 1x USB-C PD female
Output	1x HDMI-A female, 2x USB-A female, 1x USB-C female, SD and microSD card slots
HDMI Standard	HDMI 2.0
USB-C Standard	USB 3.2 Gen 1
Data Transfer Rate	Up to 5 Gbps
Compatible with Thunderbolt 3/4	Yes
Power Delivery Standard	PD 2.0
USB-C PD Port Output	5 V/3 A (15 W), 9 V/3 A (27 W), 12 V/3 A (36 W), 15 V/3 A (45 W) 20 V/5 A (100 W). Max. output: 100 W
USB Power Output	USB-A: 5 V/1 A, 5 W max.; USB-C: 5 V/3 A 15 W max.
DisplayPort Alt Mode	Yes
HDCP	1.4 to 2.3
DCDP	1.0
HDMI Output Resolution	4K/60 Hz
MST (Multi-Stream Transport)	Yes (for Windows and Mac OS)
EDID Management	Pass-through
3D Support	Yes
CEC (Consumer Electronics Control)	Yes
DDC (Display Data Channel)	Yes
ARC (Audio Return Channel)	Yes
HDR (High-Dynamic Range)	Yes
DSC (Display Stream Compression)	Yes
HFR (High Frame Rate)	Yes
TMDS (Transition Minimized Differential Signaling)	Yes

Color Format Support	RGB, YCbCr4:4:4, YCbCr4:2:2, YCbCr4:2:0
Color Depth Support	8, 10 bit per channel
Umcompressed Audio	LPCM 2.0/5.1/7.1
Compressed Audio	DTS, Dolby Digital,DTS-HD Master Audio, Dolby TrueHD
Display Mode	Main/Extend/Mirror
Supporting Memory Cards	SD/SDHC/SDXC, microSD/microSDHC/microSDXC, MMC series
Memory Card Capacity	Up to 2 TB
Power By	USB bus powered
Hot Plug/Plug & Play	Yes
Max. Power Consumption	15 W
Housing	Alumimum
Color	Grey
LED Indication	Blue (power & activity)
Operating Temperature	0–50°C
Operating Humidity	10–85% RH (no condensation)
Compatibility	Windows, Linux, Mac OS, Chrome OS, SteamOS and iPad OS
Dimensions	13 x 3.2 x 1.2 cm
Weight	45.5 g

Package Contents:
» 1x USB-C Hub
» 1x User Manual

Package Information:
» Packing Dimension: 75 x 25 x 138 mm
» Packing Weight: kg
» Carton Dimension: mm
» Carton Q'ty: pcs
» Carton Weight: kg

*The specifications and pictures are subject to change without prior notice.
*All trade names referenced are the registered trademarks of their respective owners.

UA0482
4 052792 086539
Made in China