

Adapter USB Type-C™ male to female, compatible with USB 5 / 10 / 20 / 40 Gbps and Thunderbolt™ 3 and 4 - full-featured for Video, Data and Charging

Description

This USB-C™ adapter by Delock can be used for the connection of **USB-C™ and Thunderbolt™** devices. It can be also connected to a free USB-C™ port in order to **prevent** the interface from damage when it is under usage for high contact durability.

Full-featured adapter (pass-through)

The adapter acts as a **forwarding of the original USB Type-C™ / Thunderbolt™ interface** and thus continues to provide all functions. It can transfer data up to **40 Gbps** transmission speed, power delivery is supported up to **140 watts** and the video signal is displayed up to **8K 60 Hz**.

Suitable for docking stations

Supporting all USB Type-C™ features, the adapter can be used as a port protector for USB-C™ and Thunderbolt™ docking stations.



Item no. 65697

EAN: 4043619656974

Country of origin: China

Package: Zip poly bag

Technical details

- Connectors:
 - 1 x USB 40 Gbps USB Type-C™ male
 - 1 x USB 40 Gbps USB Type-C™ female
- Data transfer rate up to 40 Gbps
- Compatible to Thunderbolt™ 3 and 4
- Transmission of audio and video signals
- Maximum resolution: 7680 x 4320 @ 60 Hz
- USB Power Delivery (PD) 3.1 up to 140 W
- Colour: black
- Metal housing
- Dimensions (LxWxH): ca. 28 x 12 x 6 mm

Package content

- Adapter

Interface

Connector 1:	1 x USB 10 Gbps USB Type-C™ male
Connector 2:	1 x USB 10 Gbps USB Type-C™ female

Technical characteristics

Data transfer rate:	10 Gbps
---------------------	---------

Physical characteristics

Length:	28 mm
Width:	12 mm
Height:	6 mm
Colour:	black

Manufacturer information

Street	Beeskowdamm 13/15
Postal code	14167
City	Berlin
Country	Deutschland
E-Mail	info@delock.de
Website	www.delock.de