



FP BF 27

IP
44

- Ventilation flange
- (recommended) alignment: vertical

CONNECTION DATA

MECHANICAL PROPERTIES

Delivered accessories:	Fastening material
IP degree of protection:	IP44
Suitable for box wall:	270 mm
(Recommended) alignment:	Vertical

AMBIENT CONDITIONS

Application area:	Indoor installation
Maximum ambient temperature 24 h:	35 °C
Ambient temperature:	-5 °C up to +40 °C
Relative humidity:	≤ 50 % at 40 °C, ≤ 100 % at 25 °C

DIMENSIONS

Height: 270 mm
Width: 33 mm
Depth: 33 mm
Net weight: 0.182 kg

CERTIFICATES

conforming to the standards: IEC 61439-3

SALES DATA

Product number: 68000195
EAN: 4012591117780
Pack unit: 1
Customs tariff number: 85371098
ETIM class: DYNAMIC: EC000331 - Ventilation plate (enclosure/cabinet)
ETIM-9.0: EC000331 - Ventilation plate (enclosure/cabinet)
ETIM-8.0: EC000331 - Ventilation plate (enclosure/cabinet)
ETIM-7.0: EC000331 - Ventilation plate (enclosure/cabinet)
ETIM-6.0: EC000331 - Ventilation plate (enclosure/cabinet)
ETIM-5.0: EC000331 - Ventilation plate (enclosure/cabinet)
ETIM-4.0: EC000331 - Ventilation plate (enclosure/cabinet)

DRAWINGS

