









5	6	7	8
REV.	ECN NO.	DATE	SIGN
DESCRIPTION			




- ① M Housing
- ② O-Ring
- ③ Nut
- ④ Ins_Housing
- ⑤ M_Pin
- ⑥ CLIP Ass'y



Pin Assignments
Front View



Conn.



Note:

- * @@Important Dimensions To Check.(重點檢查尺寸)
- * Voltage (電壓): AC 660V ; DC 1000V
- * Current (電流): 30A
- * Please refer to manual for Ass'y instruction (使用方式請參閱組裝說明書)
- * Standard (認證): ULXXXXX ;CSAXXXX; TUVXXXXX
- * Waterproof Rate(防水等級): IP68_3M6H(Mating對接)
- * Male Housing(公膠芯): m-PPE(F1),Black (黑)
- * Male Pin (公端子): Copper(銅),Tin Plated(鍍錫)
- * O-ring (O型環): Silicone (矽樹脂),Gray (灰)
- * Cable OD range (線材範圍): 16mm~13mm
- * Wire Size(導體尺寸): 10AWG~16AWG
- * Flame Class(防火等級): UL94V-0
- * One Set Unassembled in one PE Bag.
- * One Set Ass'y Instructions in one PE Bag. (每包袋子中含有未組裝零件, 組裝說明書)

UNIT:mm		TITLE PV Connector 3Pin Cable(16MM) M CON, M PIN
TOLERANCE		SCALE Free SHEET 1 OF 1
.X ±0.25		REV. A SIZE A4
.XX ±0.1		QC :Inspection Item
.XXX ±0.05		
ANGLES ±1°		

Amphenol LTW
安費諾亮泰企業股份有限公司

ITEM NO LTWPWJ-03BMMB-LL8001	DRAWN BY Micky	DATE 2011/06/13
DWG NO LTWPWJ-03BMMB-LL8001	CHECKED BY Doreen	DATE 2011/06/13
CUSTOMER	APPROVED BY Victor	DATE 2011/06/13