





Transfer or duplication of this document as well as the utilisation or communication of its content are not permitted unless express consent is granted. Violations give rise to claims for damages. All rights reserved in case of patent, utility model or design patent registrations.

Weitergabe sowie Vervielfältigung dieses Dokuments, Verwertung und Mitteilung seines Inhalts sind verboten, soweit nicht ausdrücklich gestattet. Zuwiderhandlungen verpflichten zu Schadenersatz. Alle Rechte für den Fall der Patent-, Gebrauchsmuster- oder Designeintragung vorbehalten.

depth
width
height



A-A



- General Information
- Simplified representation, exemplary shown in gray
 - Document excluded from change process
 - CAD Data see Download-Center on www.phoenixcontact.com
 - Linear dimensions [mm]
 - Tolerances, apply in a normal climate according to DIN EN ISO 291-23/50-2, with about 2% (% by weight) moisture content.

1) Marking area

⊕=Workpiece zero point for mechanical processing

 DIN A3	document-No. / RI		date	scale
	00846568 / 02		27.01.2026	1:1
	ident.-No.	document-type		
	2707495	TECDOC 2D_Productdrawing		
	description			
page 1	of 1	ME 22,5 OT-1MSTBO BK		