

D-Type Module HDMI-A female to HDMI-A female with protective cap IP67 dust and waterproof

Description

This module by Delock can be mounted e.g. in panels or cases with D-type openings for XLR jacks. This makes it ideal for integrating digital equipment into professional audio systems.

IP67 dust and waterproof

The coupler offers increased protection from dirt and moisture for the connection of the cables.



Item no. 86972

EAN: 4043619869725

Country of origin: China

Package: Zip poly bag

Technical details

- Connectors:
 - 1 x HDMI-A female
 - 1 x HDMI-A female
- For D-type ports with 31 x 25 mm
- Panel cut-out (diameter): ca. 24 mm
- Protection class: IP67
- With sealing cap
- Two mounting holes for screw fastening
- Material: plastic
- Colour: black
- Maximum resolution: 3840 x 2160 @ 60 Hz
- Dimensions (LxWxH): ca. 30.0 x 31.0 x 26.0 mm

Package content

- D-Type module

Images



General

Mounting type:	D-Type
Style:	both sides identical

Interface

Connector 1:	1 x HDMI-A female
Connector 2:	1 x HDMI-A female

Technical characteristics

Maximum screen resolution:	3840 x 2160 @ 60 Hz
----------------------------	---------------------

Physical characteristics

Housing material:	Plastic
Length:	30.0 mm
Width:	31.0 mm
Height:	26.0 mm
Colour:	black

Manufacturer information

Street	Beeskowdamm 13/15
Postal code	14167
City	Berlin
Country	Deutschland
E-Mail	info@delock.de
Website	www.delock.de

